Straight Blade Devices 30A, 3 Phase Y 120/208V AC, 4 Pole, 4 Wire Non-Grounding

HUBBELL

Plug

Features

- Catalog number, ratings and certifications molded in face
- Gripping ribs provide secure gripping area
- Supertough nylon housing



Ordering Information

Catalog Number Cord Diameter Description **UPC** Plug, nylon .625"-1.310" 783585015460 HBL8331C (15.9-33.3)

Listings

UL Listed File E1706 Certified to CSA

Specifications

Housing Supertough Nylon

Blade Holder Reinforced Thermoplastic Polyester Blades **Brass Box Terminals** Copper Alloy

Cord Clamps Reinforced Thermoplastic Polyester

[104.8] HUBBELL Ø 288 [73.0] CORD GRIP RANGE Ø.625 TO Ø1.310 [15.88] [33.27]

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Withstands 2,000V minimum Dielectric Voltage

Mechanical

Product Identification Ratings are a permanent part of the device **Terminal Accommodation** #12 AWG through #4 AWG copper wire only

Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

UL 94 HB Flammability IP Suitability IP20

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)

Resources

Customer Use Drawing eCatalog

