Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hospital Grade Valise® Plug

HUBBELL

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors

Ordering Information

Description White nylon	Cord Diameter .300"660" (7.6-16.8)	UPC 783585016337	Catalog Number HBL8364V
	(7.0-10.0)		



Listings

UL Listed to UL498 File No. E2186 Certified to CSA, C22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant

Specifications

Housing	Nylon	
Blades	Brass	
Assembly Screws	Plated Steel	
Cable Inserts	PPO	

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2000V AC minimum

Mechanical

Product Identification Ratings are a permanent part of the device


Terminal Accommodation #16 to #12 AWG

Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94 HB IP Suitability IP20

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



Resources

Customer Use Drawing eCatalog

