Straight Blade Devices 30A, 3 Phase 250V AC, 3 Pole, 4 Wire Grounding Single Receptacle

Features

- Sequenced contacts assure protection
- Catalog number, ratings and certifications molded in face
- One piece design power and ground contacts

Ordering Information

Description	Device Color	UPC	Catalog Number
Receptacle, black RTP	Black	783585015149	HBL8430A

Listings

UL Listed File E2186 Certified to CSA NEMA® WD-6 Compliant

Specifications

Housing	Nylon
Contacts	Brass
Ground Shunt	Brass

Mounting Plate .062 in. (1.5) Pre-Plated steel

Box Terminals Copper

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #12 AWG through #4 AWG copper wire only

Terminal Identification Terminals identified in accordance with UL 498 and CSA


Environmental

Flammability UL 94 V-0 IP Suitability IP20

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)

HUBBELL





Accessories

Wallplate or Weatherproof Cover 2.48" Opening

Resources

Customer Use Drawing eCatalog

