Twist-Lock® Devices 20A, 250V AC, 2 Pole, 2 Wire Non-Grounding Insulgrip® Flanged Receptacle

HUBBELL

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #8-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Ordering Information

Description Device Color UPC Catalog Number Nylon casing, back White 783585180601 HBL8809C wired.

Listings

Listed to UL 498 Fed Spec W-C-596

Specifications

Housing Nylon

Terminal Retainer Clear polycarbonate

Contacts Brass

Terminal Clamp #8-32 Brass (Phillips / Slotted / Robertson)

Terminal Clamp Cold rolled steel – nickel plated

Assembly Screws Steel - zinc plated Mounting Screw Nickel plated brass

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 - #10 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental


Flammability HB or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)







Accessories

Plug HBL7102C Weatherproof Lift Cover WP1

Resources

Customer Use Drawing Customer Use Drawing eCatalog

