Insul-Lock™ Connectors 25 Amp Connector

HUBBELL

Features

- · Insulgrip style body design
- Accepts up to #12/3 AWG SO cable
- · Industry standard mating
- Quick Release Latch
- Multiple strain relief collets to accommodate wide range of cable

Ordering Information

DescriptionUPCCatalog NumberPower In, 25 Amp, Inline783585539089HBLCPIBLConnector

Cord Size Color Accepts # 14/3 SJ up to #12/3 Blue

AWG SO cable

Listings

cULus

UL Recognized Component rated up to 25A per UL 1977

cUL Recognized Component rated up to 25A per Canadian National Standard C22.2 No. 182.3

Suitable for use in UL 1640 applications

Specifications


Body Thermoplastic
Contacts Copper Alloy
Weight 0.07

Performance

Electrical

Amperage 25A Voltage up to 250V





Complementary Products

25 Amp Connector

HBLPMIBL, HBLPMIDBL

Online Resources

eCatalog

