Insul-Lock™ Connectors 25 Amp Connector

HUBBELL

Features

- · Insulgrip style body design
- Accepts up to #12/3 AWG SO cable
- Industry standard mating
- Quick Release Latch
- Multiple strain relief collets to accommodate wide range of cable

Ordering Information

UPC Description **Catalog Number** Power out, 25 Amp, Inline 783585539096 **HBLCPOGY** Connector

Cord Size Color Accepts # 14/3 SJ up to #12/3 Gray

AWG SO cable

Listings

cULus

UL Recognized Component rated up to 25A per UL 1977

cUL Recognized Component rated up to 25A per Canadian National Standard C22.2

Suitable for use in UL 1640 applications

Specifications


Body Thermoplastic Contacts Copper Alloy Weight 0.07

Performance

Electrical

Amperage 25A up to 250V Voltage





Complementary Products

25 Amp Connector

HBLPMOGY, HBLPMODGY

Online Resources

eCatalog

