Switched Disconnects and Enclosures

Non-Metallic Replacement Covers

HUBBELL

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Reversible interior accomodates top or bottom conduit opening

Ordering Information

Description 100A Replacement Cover for Disconnect Switch **UPC Number** 783585912462

Catalog Number HBLDS10RC

Specifications

Cover PBT Handle PBT

Cover & Handle Screw Stainless Steel
Gasket Neoprene

Performance

Dielectric Voltage

Max. Working Voltage

Electrical

Current Interrupting Certified for current interrupting at full rated

current and voltage

Withstands 3000V AC minimum

600V AC RMS

Mechanical

Impact Resistance In accordance with UL 746C Mounting External fully adjustable feet

Terminal Identification In accordance with UL, CSA and international

conventions

Environmental Flammability

Indoor and Outdoor — Type 4X (Wash down, Corrosion resistant); Indoor — Type 12 (Dust-tight, Falling Dirt, Noncorrosive Liquids).

Moisture Resistance

Worstare reconstance

Operating Temperature

UL94-5VA and V0 Classification

Max. Continous: 75°C; Min. Continuous: -40°C


without impact

Indoor and Outdoor – Type 4X (Wash down, Corrosion resistant); Indoor – Type 12 (Dust-tight, Falling Dirt, Noncorrosive Liquids).

Max. Continous: 75°C; Min. Continuous: -40°C

without impact





Complementary Products

Non-Metallic Labelless Circuit-Lock® Switched Disconnect

HBLDS10; HBLDS10AC; HBLDS10VFD

Online Resources

Customer Use Drawing eCatalog

Installation Instructions

