Switched Disconnects and Enclosures

Non-Metallic Replacement Covers

HUBBELL

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Reversible interior accommodates top or bottom conduit opening

Ordering Information

Description **UPC Number Catalog Number** 60A Replacement Cover for HBLDS6RC 783585912455 Disconnect Switch



Specifications

Cover PBT PBT Handle Cover & Handle Screw Stainless Steel

Performance

Electrical

Certified for current interrupting at full rated Current Interrupting

current and voltage

Dielectric Voltage Withstands 3000V AC minimum Max. Working Voltage

600V AC RMS

Mechanical

In accordance with UL 746C Impact Resistance Mounting External fully adjustable feet

Terminal Identification In accordance with UL, CSA and international

conventions

Environmental

Dirt, Noncorrosive Liquids).

Operating Temperature

Flammability UL94-5VA and V0 Classification

Indoor and Outdoor - Type 4X Max. Continous: 75°C; Min. Continuous: -40°C (Wash down, Corrosion resistant); without impact

Indoor - Type 12 (Dust-tight, Falling


Indoor and Outdoor - Type 4X (Wash down, Moisture Resistance

Corrosion resistant); Indoor - Type 12

(Dust-tight, Falling Dirt, Noncorrosive Liquids).

Max. Continous: 75°C; Min. Continuous: -40°C

without impact



Complementary Products

Non-Metallic Labelless Circuit-Lock® Switched Disconnect Enclosures

HBLDS6; HBLDS6VFD; HBLDS6AC

Online Resources

Customer Use Drawing eCatalog

Installation Instructions

