## Single Pole Devices and Temporary Power 300 and 400A, 600V AC/DC

# HUBBELL

## **Angled Receptacles, Stud Type Through Hole** Mounting

#### **Ordering Information**

Description 400 amp Panel Mount, thermoplastic elastomer, mates with 300 and 400 amp Inlines.

Color Brown **UPC** 783585511603 **Catalog Number HBLFRASBN** 

#### Listings

UL and cUL Listed UL Enclosure Types 3R, 4X, 12 National Electric Code (NEC), ANSI/NFPA 70

### **Specifications**

Base Compound Thermoplastic Elastomer (TPE)

**Contact Material Brass** Retaining Screw Material Nylon Mounting Hole 4x #10-32

Termination (2) 7/32 Socket Head Set Screws

## **Performance**

Electrical

Amperage Rating 400A Maximum Voltage Rating 600V AC/DC Maximum

Mechanical

**Product Identification** Ratings are a permanent part of device

**Terminal Accommodation** #4 to 4/0 AWG

**Environmental** 

HB per UL94 or CSA 22.2. 0.17 Flammability



#### **Online Resources**

**Customer Sales Drawings** eCatalog Installation Instructions

