Single Pole Devices and Temporary Power 400A, 600V AC/DC

Female Receptacles

HUBBELL

Ordering Information

Description

400A, thermoplastic elastomer, cable size #4 -4/0 AWG, mates with 300A&400A Plugs.

Device Color Blue

UPC Number 783585112602 **Catalog Number HBLFRBL**

Listings

UL and cUL Listed UL Enclosure Types 3R, 4X, 12 National Electric Code (NEC), ANSI/NFPA 70

Specifications

Base Compound

Thermoplastic Elastomer

Contact Material Retaining Screw Material Brass Nylon 4x #10-32

Mounting Hole Termination

(2) 7/32 Socket Head Set Screws

Performance

Electrical

Amperage Rating Voltage Rating

400A Maximum

600V AC/DC Maximum

Mechanical


Product Identification **Terminal Accommodation** Ratings are a permanent part of device

#4 to 4/0 AWG

Environmental

Flammability HB per UL94 or CSA 22.2. 0.17





Online Resources

Customer Sales Drawings eCatalog Installation Instructions

