

## Single Pole Devices and Temporary Power

400A, 600V Series 16

# Extended Stud Type Female Receptacles

# HUBBELL

## Ordering Information

Description	Device Color	UPC	Catalog Number
400 A, Panel Mount, thermoplastic elastomer, mates with 300 and 400A plugs	Green	783585433899	HBLFRSCEGN

## Standards

UL and cUL Listed  
UL Enclosure Types 3R, 4X, 12  
National Electric Code (NEC), ANSI/NFPA 70

## Specifications

Base Compound	Thermoplastic Elastomer
Contact Material	Brass
Retaining Screw Material	Nylon
Mounting Hole	4x Ø .20"
Termination	1/2-13 UNC-2A Threaded Stud

## Performance



<b>Electrical</b>	
Amperage Rating	400A Maximum
Voltage Ratings	600V Maximum

<b>Mechanical</b>	
Product Identification	Ratings are a permanent part of device

<b>Environmental</b>	
Flammability	HB per UL94 or CSA 22.2. 0.17

## Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions



Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

