

Locking Devices

Insul-Lock Plus Devices

20A Connector

HUBBELL

Features

- Insulgrip style body design
- Accepts up to #12/3 AWG SO cable
- UL Enclosure type 4X and IP65 rated
- Disconnectable under load
- Multiple strain relief collets to accommodate wide range of cables
- Industry standard mating

Ordering Information

Description	UPC	Catalog Number
Locking male cable connector, power out, screw terminals	783585580869	HBLMC
Cord Size	Color	
Accepts #18/3 up to #12/3 AWG SO Cable	Black	

Listings

UL Recognized to US and Canadian standards
UL50E Encl. type 4X when mated to Insul-lock plus HBLFC
or when mated to HBLFP or HBLFPD in combination with HBLFPC or HBLFPDC
IP65 rated when mated to Insul-lock plus HBLFC
or when mated to HBLFP or HBLFPD in combination with HBLFPC or HBLFPDC

Specifications

Body	Thermoplastic
Contacts	Copper Alloy
Weight	0.1

Performance

Electrical	
Amperage	20A
Voltage	up to 250V AC



Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

