Watertight Devices

Accessories

Portable Outlet Boxes and Cover Plates

Features

Impact resistant cover plate

Ordering Information

Description	Cord Diameter	
Box with cord strain relief, with two	.38" to .75"	
duplex cover plates.		

UPC 783585681856 Catalog Number HBLPOB1DL





Standards

UL 514C, UL467 and UL50 Enclosures Types 1, 3R C22.2 No. 18 and C22.2 No. 94 Enclosures Types 1, 3R and C22.2 No. 0.4


Specifications

Cord Connector

Bonding Strap Grounding Screw Gasket Indoor Screws

Nylon nut; Nylon Gotcha® ring; Neoprene grommet Brass Brass UL recognized closed-cell foam Zinc Plated Steel





Performance

Moisture Resistance

Operating Temperature UV Resistance

Environmental Flammability Impact and Crush Resistance

UL 94V-0, 94-5VA classification In accordance with UL 514C, UL50, C22.2 No. 18 and C22.2 No. 94. Wet and damp locations, Enclosure Type 3R when used with weatherproof cover plates.Dry, indoors locations, Enclosure Type 1 with all other cover plates 80°C maximum; -35°C minimum All materials are UV stabilized

Online Resources

Customer Use Drawing eCatalog Installation Instructions

