## **Watertight Devices**

#### **Accessories**

# **Portable Outlet Boxes and Cover Plates**

# HUBBELL

#### **Features**

• Impact resistant Valox® cover plate

# **Ordering Information**

Description **Cord Diameter UPC Catalog Number** Box with cord strain relief, with two HBLPOB1D .38" to .75' 783585318110 duplex cover plates.

#### **Standards**

UL 514C, UL467 and UL50 Enclosures Types 1, 3R C22.2 No. 18 and C22.2 No. 94 Enclosures Types 1, 3R and C22.2 No. 0.4

### **Specifications**

Cord Connector Nylon nut; Nylon Gotcha® ring; Neoprene

grommet **Brass** 


**Bonding Strap Grounding Screw** Brass

Gasket UL recognized closed-cell foam

Indoor Screws Zinc Plated Steel







# **Performance**

**Environmental** 

UL 94V-0, 94-5VA classification Flammability Impact and Crush Resistance

In accordance with UL 514C, UL50, C22.2 No. 18

and C22.2 No. 94.

Moisture Resistance Wet and damp locations, Enclosure Type 3R when used with weatherproof cover plates. Dry, indoors

locations, Enclosure Type 1 with all other cover

Operating Temperature **UV** Resistance

80°C maximum; -35°C minimum

All materials are UV stabilized

## **Online Resources**

Customer Use Drawing eCatalog

Installation Instructions

