Watertight Devices

Accessories

Portable Outlet Boxes and Cover Plates

Features

· Impact resistant cover plate

Ordering Information

Description **Cord Diameter UPC Catalog Number** Box with cord strain relief, with one 783585681887 HBLPOB1L .38" to .75' blank cover plate.

Standards

UL 514C, UL467 and UL50 Enclosures Types 1, 3R C22.2 No. 18 and C22.2 No. 94 Enclosures Types 1, 3R and C22.2 No. 0.4 UL listed for pendant or feed through mounting, File E92074

Specifications

Cord Connector Nylon nut; Nylon Gotcha® ring; Neoprene

grommet

Bonding Strap Brass Grounding Screw Brass

Gasket UL recognized closed-cell foam

Indoor Screws Zinc Plated Steel

Performance

Environmental

Flammability UL 94V-0, 94-5VA classification Impact and Crush Resistance

In accordance with UL 514C, UL50, C22.2 No. 18

and C22.2 No. 94.

Moisture Resistance Wet and damp locations, Enclosure Type 3R when used with weatherproof cover plates. Dry, indoors

locations, Enclosure Type 1 with all other cover

Operating Temperature 80°C maximum; -35°C minimum

UV Resistance All materials are UV stabilized

Online Resources

Customer Use Drawing eCatalog

Installation Instructions

HUBBELL









