

**Switch-Rated IEC Style Pin and Sleeve**  
**30A, 600V Max, 3-Pole 4-Wire Grounding**  
**Watertight Receptacle**

# HUBBELL

## Features

- Approved As a disconnecting means for motor circuits and branch circuits
- 3 early break control contacts rated a 3A 120V AC/24DC
- Unswitched feed-thru ground is first to mate and last to break
- Superior HP Rating and SCCR
- Type 4X, 12 & IP69K environmental rating



## Ordering Information

Description	UPC	Catalog Number
Watertight Receptacle	783585679884	HBL5430R7WC

## Listings

UL Listed, File E146032  
CSA Certified File LR280C

## Related Products

Cover Assemblies

## Specifications

Locking Ring	PBT
Sealing Gasket	Solid Neoprene
Covers	PBT
Gaskets	Santoprene
Contact Carrier	Nylon
Housing	PBT

## Online Resources

eCatalog

## Performance

### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstand 3000V AC
Max. Working Voltage	600V AC RMS

### Mechanical

Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Identification and ratings are a permanent part of the device housing.
Terminal Identification	Terminals identified in accordance with North American and IEC conventions

### Environmental

Flammability	V-0
Ingress Protection	Type 3R,3RX,4X and IP68,IP69K
Moisture Resistance	IEC 60309-1
Operating Temperatures	Maximum Continuous 75°C; Minimum - 40°C w/o impact

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

