Temporary Power Temporary Industrial Lighting LED Maintenance Worklights



Features

- Inline Tool Tap with hinged outlet cover to keep dirt and debris out
- Covered on/off switch in handle controls side and end LEDs
- Polycarbonate outer tube is extremely durable

Ordering Information

Description UPC Catalog Number
LED work light with 783585467412 HBLWL25LEDT
end light feature & tool
tap



Listings

UL

Online Resources

eCatalog

Specifications

Outer Tube Material Polycarbonate
Hook Material Steel
Light Type LED
Plug Type NEMA 5-15P
Length 10.25
Width 1.75
Included 1 Attached hanging hook

Performance

Electrical

 Lamp Life
 50,000 hours

 Light Angle Degree
 130

 Light Color
 4700-5200 K

 Lumen Output Side/End
 920/120

 Rating
 15A 125V

 Wattage
 9

Mechanical

Cord Length 25 ft.
Cord Type 16/3 SJTOW

