

Temporary Power Temporary Industrial Lighting LED Maintenance Worklights

HUBBELL

Features

- Two 4-watt high output LEDs provide a nice even light
- Covered on/off switch in handle controls side and end LEDs
- Polycarbonate outer tube is extremely durable

Ordering Information

Description	UPC	Catalog Number
LED work light with end light feature	783585467429	HBLWL25LED



Listings

UL

Online Resources

[eCatalog](#)

Specifications

Outer Tube Material	Polycarbonate
Hook Material	Steel
Light Type	LED
Plug Type	NEMA 5-15P
Length	10.25
Width	1.75
Included	1 Attached hanging hook

Performance

Electrical

Lamp Life	50,000 hours
Light Angle Degree	130
Light Color	4700-5200 K
Rating	15A 125V
Wattage	9

Mechanical

Cord Length	25 ft.
Cord Type	18/2 SJTOW

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

