

Temporary Power Temporary Industrial Lighting Hazardous Location Lights

HUBBELL

Features

- Equal to a 75-watt light bulb, the STUBBY II fluorescent light is watertight (not submersible), compact and durable
- A reflector inside the outer tube directs maximum light to the work surface
- The on-off switch located under the handle end cap is protected from dirt and moisture

Ordering Information

Description	UPC	Catalog Number
Fluorescent, non-explosion proof, watertight 12V, inline transformer	783585467337	HBLWT6012V

Listings

UL
CSA
ETL

Specifications

Light Type	Fluorescent
Plug Type	NEMA 5-15P
Length	11
Width	1.75

Performance

Electrical	
Inline Transformer	12V
Lamp Life	10,000 hours
Light Color	5000 K
Lumen Output	825
Wattage	13

Mechanical	
Cord Length	60 ft.
Cord Type	18/2 SJTOW

Environmental	
Watertight	Yes



Online Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

