

Temporary Power
Temporary Industrial Lighting
Hazardous Location Lights



Features

- Designed for Class 1, Division 1, Groups C & D hazardous locations
- No plug included to allow flexibility for user
- Outer shell is corrosion resistant, non-sparking, and comes with rotating hook



Ordering Information

Description	UPC	Catalog Number
Incandescent, Class 1, Div 1 Groups C & D, 120V less plug	783585467320	HBLXI50120V

Listings

UL
CSA
ETL

Online Resources

eCatalog

Specifications

Light Type	Incandescent
Plug Type	No Plug
Length	18
Width	5

Performance

Electrical	
Lamp Life	1,000
Light Color	2700 K
Lumen Output	1230
Rating	120V
Wattage	100
Mechanical	
Cord Length	50 ft.
Cord Type	16/3 SOW

