

Temporary Power Temporary Industrial Lighting Hazardous Location Lights

HUBBELL

Features

- Designed for Class 1, Division 1, Groups C & D hazardous locations
- Inline transformer can be placed outside hazardous zone while light is used inside zone and still remain code compliant
- Outer shell is corrosion resistant, non-sparking, and comes with rotating hook
- 360 degree area lighting



Ordering Information

Description	UPC	Catalog Number
Incandescent, Class 1, Div 1, Groups C & D, 12V, inline transformer	783585467306	HBLXI6012V

Listings

UL
CSA
ETL

Online Resources

[eCatalog](#)

Specifications

Light Type	Incandescent
Plug Type	NEMA 5-15P
Length	18
Width	5

Performance

Electrical

Inline Transformer	12V
Lamp Life	1,000
Light Angle Degree	360
Light Color	2700 K
Lumen Output	720
Wattage	75

Mechanical

Cord Length	60 ft.
Cord Type	16/3 SOW

Environmental

Explosion Proof	Class 1, Div 1 Groups C & D
-----------------	-----------------------------

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

