

Wire Basket Tray Tray Section Overhead Tray, 118" Length

HUBBELL

Features

- For use in control environments
- Top rail T-weld construction prevent snags
- Flat shaped cross wire provides more cable support area



Ordering Information

Height	Width	Catalog Number	UPC Number
4"	24"	HBT0424S	783585416700

Standards

UL Classified as equipment grounding conductor
ASTM A 641

Specifications

Material	100% Recycled Steel
Finish	Pre-Galvanized
Flat Shaped Cross-Wires	Cable Support Area- .03125 square inch
Mesh Spacing	2" x 4" (50.5 x 101.6)

Performance

No-Splice Support Spacing	5' (1524)
Splice Kit Qty- 90 Degree Sweep Elbow	12
Splice Kit Qty- Straight Splice	8
Support Spacing	6' (1828.8)
Tray Area (cu. in.)	96
Weight Capacity (lb/ft)	116

Dimensions- inches (mm)

Height	4" (102)
Width	24" (610)
Length	118" (2997.2)

Accessories

Angled Cutting Tool	HBTCUTTOOL
Splice Kit	HBTSK
Corner Splice	HBTCSS
Pre-Galvanized Steel Cover	HBTCVR24
Pre-Galvanized Steel Divider	HBTDIV4

Online Resources

eCatalog

