

# Wire Basket Tray Tray Section Overhead Tray, 118" Length

# HUBBELL

## Features

- For use in control environments
- Top rail T-weld construction prevent snags
- 5mm round wire minimum

## Ordering Information

| Height | Width | Catalog Number | UPC Number   |
|--------|-------|----------------|--------------|
| 8"     | 20"   | HBT0820        | 783585417240 |



## Standards

UL Classified as equipment grounding conductor  
ASTM A 641

## Specifications

|              |                        |
|--------------|------------------------|
| Material     | 100% Recycled Steel    |
| Finish       | Pre-Galvanized         |
| Mesh Spacing | 2" x 4" (50.5 x 101.6) |

## Performance

|                                       |             |
|---------------------------------------|-------------|
| No-Splice Support Spacing             | 5' (1524)   |
| Splice Kit Qty- 90 Degree Sweep Elbow | 9           |
| Splice Kit Qty- Straight Splice       | 9           |
| Support Spacing                       | 6' (1828.8) |
| Tray Area (cu. in.)                   | 160         |
| Weight Capacity (lb/ft)               | 116         |

## Dimensions- inches (mm)

|        |               |
|--------|---------------|
| Height | 8" (203)      |
| Width  | 20" (508)     |
| Length | 118" (2997.2) |

## Accessories

|                              |            |
|------------------------------|------------|
| Angled Cutting Tool          | HBTCUTTOOL |
| Splice Kit                   | HBTSK      |
| Corner Splice                | HBTC       |
| Pre-Galvanized Steel Cover   | HBTCVR20   |
| Pre-Galvanized Steel Divider | HBTDIV8    |

## Online Resources

eCatalog