

Power and AV Enclosures

AV In-Wall and Ceiling Enclosures

Power and AV Wall Enclosures

HUBBELL

Features

- 16 gauge steel back box with black two piece cover
- 2" conduit feed-through with 1" and 1-1/2" concentric knockouts
- Four old work box knockouts for top or bottom feed
- 2" x 4" x 16" on-center flush mounting
- Can also be used as in-wall storage box

Ordering Information

Description	Color	UPC	Catalog Number
Recessed Wallbox, 5-Gang, 2" Conduit feed-Thru, Black	Black	783585695792	HRWB25BLK



Listings

cETLus Listed
Conforms to UL 62368-1:2019 Ed.3
Certified to CSA C22.2#62368-1:2019 Ed.3

Specifications

Box Material	16 Gauge Pregalvanized Steel
Cover Material	Steel
Cover Finish	Black paint
Box Dimensions in (mm) (H x W x D)	7.24" (183.8) x 14.25" (362.0) x 4.00" (141.6)
Cover Dimensions in (mm) (H x W x D)	8.34" (211.7) x 15.50" (393.7) x 0.16" (4.0)
Cover Paintable	Yes

Related Products

3/4" masonry, steel and wood frame box extension HRWB25BE075

Surge Protected Power Kit NSOKPS
Power Kit NSOKPTR
1-Gang, 6-Port Multimedia Face Plate, IFP16GY
Gray

1-Gang, 6-Port Multimedia Face Plate, IFP16W
White

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

