
# **Z-Wave In-wall Smart Switch**







## **Specifications**

Power: 120VAC, 60Hz Signal Frequency: 908.4/916MHz

Maximum Load: 960W Incandescent, 1/2 HP Motor 1800W (15A Resistive)

Range: Up to 150 feet from controller or closest Z-Wave device

Operating Temperature: 32-104° F (0-40° C) Warranty: 5-year limited product warranty

Requires neutral wire. Switch must be mounted indoors

## Design Features

- · Turn the connected device On/Off manually or via Z-Wave hub or controller
- · Remotely monitor with any mobile device\*
- · Works with Google and Alexa (requires compatible hub\*
- · May be used in single pole installation or with up to four iDevices® model IDEVZ03DW Add-on switches in 3, 4, 5 or 6-way wiring configurations
- · Works with all LED, CFL, halogen and incandescent bulbs
- · Blue LED indicates switch location in a dark room (with 4 adjustable settings)
- · Can be included in multiple Groups and Scenes
- · Utilizes the Z-Wave Firmware Update Meta Data command class for standardized firmware updates Over the Air
- · Supports Advanced Configuration; LED status, Alternate exclusion
- · Screw Terminal installation; requires wiring connections for Line (Hot), Load, Neutral, and Ground. Traveler wire required for multi pole installation
- Uses a standard decora wall plate (wall plate not included)
- · Interchangeable Paddle switch: White & light almond paddle included in package
- · LED status can be inverted manually changed to invert, always OFF and always ON
- · Inline traveler circuit protection
- · Z-Wave Plus Certified

2.63"

### Z-Wave Plus with S2 Security and SmartStart Features

- · Improved battery life and up to 50 percent greater wireless range
- QR codes with unique, industry-standard secure key exchange to add a layer of 128-bit encryption
- · Effortless device pairing to Z-Wave S2 and SmartStart certified gateways
- · Backward compatible with all generations of Z-Wave devices
- · 250% faster processor
- · 400% more memory
- · 50% more energy efficient
- · Supports wireless upgrades to future-proof your home

#### White/light almond paddles included





## **IDEVZ01DW** PRODUCT SPECIFICATIONS

# **Device Configuration**

#### Adding your device to a Z-Wave network

Once the hub is ready to add your smart dimmer, press and release the top or bottom button on the smart dimmer to add it in the network.

#### To remove and reset the device

Once the controller is ready to remove your device, press and release the top button on the smart dimmer to remove it from the network.

#### S2 + SmartStart install

The controller's app will indicate if it has discovered the device. If prompted by the controller to enter the S2 security code, refer to the QR code/security number on the side of the box, or the QR code label on the product. Enter the 5-digit code.



#### To return to factory defaults

Quickly press the ON button 3 times, then press the OFF button 3 times. The LED will flash ON/OFF 5 times when completed successfully.

## **Certifications & Compliances**







Compliances, specifications and availability are subject to change without notice.

DISTRIBUTED BY
WIRING DEVICES-KELLEMS
HUBBELL INCORPORATED
(DELAWARE)
SHELTON, CT 06484
©Hubbell | IDEVZ01DW | 2021 v1.1

#### Related Products - iDevices® Z-Wave Products



IDEVZ05DW In-Wall Smart Dimmer



IDEVZ03DW Add-On Switch



IDEVZ08W Smart Tamper Resistant Receptacle

