
# In-wall Add-On Switch







# Specifica ions

Power: 120/277VAC, 60Hz

Operating Temperature: 32-104° F (0-40° C) Warranty: 5-year limited product warranty Switch must be mounted indoors

### **Design Features**

- · iDevices® model IDEVZ03DW for use in 3, 4, 5, or 6-way wiring configurations with:
- iDevices® models, IDEVZ01DW and IDEVZ05DW
- Requires wiring connections Neutral, Traveler and Ground
- · Uses a standard decorative wall plate (wall plate not included)
- Maximum number of Add-On Switches connected to primary switch: 4
- Maximum traveler wire distance: 300ft., interconnected between 4 Add-On switches
- · No more than 75ft between each switch
- Maximum traveler wire distance between primary and (1) Add-On switch: 200ft
- · Not for direct control of load (Not a standalone switch)
- · Requires iDevices® Smart Control for operation

#### Related Products - iDevices® Z-Wave Products



IDEVZ05DW In-Wall Smart Dimmer



IDEVZ01DW In-Wall Smart Switch



IDEVZ08W Smart Tamper Resistant Receptacle

# White/light almond paddles included



## Certifica ions & Compliances



Compliances, specifications and availability are subject to change without notice.

DISTRIBUTED BY WIRING DEVICES-KELLEMS HUBBELL INCORPORATED (DELAWARE) SHELTON, CT 06484

©Hubbell | IDEVZ03DW | 2021 v1.1

