# Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding Commercial Specification Grade Duplex Receptacles

# Features

- Triangle marking on face indicates isolated ground
- Smooth face
- Triple wipe contacts

# **Ordering Information**

Description	Device Color	UPC	Catalog Number
Isolated ground, smooth face, side	lvory	783585147581	IG15CRI
wired only			

### Listings

UL Listed to UL498 File No. E2186 Certified to CSA C22.2, No. 42 Fed. Spec. W-C-596 NEMA® WD-6 Compliant

## **Specifications**

Face	Nylon
Base	Nylon
Power Contacts	.030 in. (.8) Brass
Ground Contacts	Brass
Wire Clamp	.062 in. (1.6) Nickel plated steel
Terminal Screws	Plated steel
Mounting Strap	.040 in. (1) Galvanized steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Galvanized Steel

Withstands 2,000V minimum

# Performance

Electrical

Current Interrupting Dielectric Voltage

#### Mechanical

Product Identification Terminal Accommodation Terminal Identification

**Environmental** Flammability Operating Temperatures UL 94 V-2 Maximum continuous 75°C; minimum -40°C (w/o impact)


#14-#10 AWG copper stranded or solid conductor only Terminals identified in accordance with UL 498 and CSA

Certified for current interrupting at full rated current

Ratings are a permanent part of the device



HUBBELL



### Accessories

Wallplate or Weatherproof Cover Duplex Opening

### Resources

Customer Use Drawing eCatalog

