# Twist-Lock® Devices 15A, 125V, 2 Pole, 3 Wire Grounding

# **Isolated Ground Receptacle**

#### **Features**

- Reinforced thermoplastic construction
- · Single piece, all brass contacts
- · Single point break-off tabs
- · Mounting strap tabs lock the body and base together

**Ordering Information** 

Description	Device Color	UPC	Catalog Number
Duplex, isolated	Orange	783585002392	IG4700A

### Listings

Listed to UL 498 Fed. Spec. W-C-596 Certified to CSA C22.2 No.42

## **Specifications**

Face	Nylon
Base	RTP
Contacts	Brass
Clamp	Brass
Ground Contact	Brass
Terminal Screws	Brass

#### **Performance**

**Electrical** 

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #18 AWG - #10 AWG solid or stranded copper wire.

Terminal Identification Terminals identified in accordance with UL 498

**Environmental** 

Flammability HB or better per UL94/CSA 22.2 No.0.17


Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)

# HUBBELL







#### **Online Resources**

Customer Use Drawing eCatalog
Installation Instructions

#### Accessories

Plug	HBL4520C
Wallplate or Weatherproof Cover	<b>Duplex Openi</b>

