

IEC Pin and Sleeve
Watertight Devices
Receptacle/Connector Replacement Interior



- Features
- Sequential contact engagement

Ordering Information

Description	UPC	Catalog Number
Pin and Sleeve Replacement Interior, For 3W 30A, IEC	783585420165	IN330AF

Device Color
Black



Standards

UL Listed
CSA Certified

Specifications

Gaskets	Neoprene
Hinge Spring	Stainless Steel
Contact Carrier	High-Impact Thermoset
Terminal Screws	Stainless Steel
Assembly Screws	Stainless Steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current

Dielectric Voltage	Withstands 3,000V AC
Max Working Voltage	600V AC RM

Mechanical	
Impact Resistance	In accordance with UL746C
Product Identification	Identification and ratings are a part of the external label and molded into the receptacle mount
Terminal Identification	Terminals identified in accordance with North American and International conventions

Environmental	
Flammability	UL94-5VA and V-0 classification
Ingress Protection	IP67 Suitability
Operating Temperatures	Max. Continuous:75°C; Min. Continuous:-40°C w/o impact

Online Resources

eCatalog

