IEC Pin and Sleeve

Watertight Devices

Plug/Inlet Replacement Interior

HUBBELL

Features

Thermoset Polyester Contact Carrier

Ordering Information

DescriptionPin and Sleeve Replacement

Interior, For 4W 100A, IEC

Device Color Black **UPC** 783585420653

Catalog Number IN4100DM



Standards

UL Listed CSA Certified

Specifications

Gaskets Neoprene
Hinge Spring Stainless Steel

Contact Carrier High-Impact Thermoset
Retainer High-Impact Thermoset
Terminal Screws Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC Max Working Voltage 600V AC RMS

Mechanical

Impact Resistance In accordance with UL746C

Product Identification Ratings are a part of the external label and molded

into the receptacle mount

Terminal Identification Terminals identified in accordance with North

American and International conventions

Environmental

Flammability UL94-5VA and V-0 classification

Ingress Protection IP67 Suitability

Operating Temperatures Max. Continuous:75°C; Min. Continuous:-40°C w/o

impact

Online Resources

eCatalog

