

**IEC Pin and Sleeve  
Watertight Devices  
Plug/Inlet Replacement Interior**

# HUBBELL

## Features

- Thermoset Polyester Contact Carrier

## Ordering Information

|   |                            |   |
|---|----------------------------|---|
| <b>Description</b><br>Pin and Sleeve Replacement<br>Interior, For 4W 60A, IEC | <b>UPC</b><br>783585420431 | <b>Catalog Number</b><br><b>IN460CM</b> |
|---|----------------------------|---|

**Device Color**  
Black



## Standards

UL Listed  
CSA Certified

## Specifications

|                 |                       |
|-----------------|-----------------------|
| Gaskets         | Neoprene              |
| Hinge Spring    | Stainless Steel       |
| Contact Carrier | High-Impact Thermoset |
| Retainer        | High-Impact Thermoset |
| Terminal Screws | Stainless Steel       |

## Performance

### Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC  
Max Working Voltage 600V AC RMS

### Mechanical

Impact Resistance In accordance with UL746C  
Product Identification Ratings are a part of the external label and molded into the receptacle mount  
Terminal Identification Terminals identified in accordance with North American and International conventions

### Environmental

Flammability UL94-5VA and V-0 classification  
Ingress Protection IP67 Suitability  
Operating Temperatures Max. Continuous:75°C; Min. Continuous:-40°C w/o impact

## Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

