

## Aluminum Ladder Tray

### Tray Section

### NEMA VE1, 12B Load Class

# HUBBELL

#### Features

- Listed to NEMA VE 1 to allow for maximum spans and weight loading.
- For use indoors and also outside in harsh environments.
- Rungs are welded to stringers for strength and continuity.

#### Ordering Information

Height	Width	UPC Number	Catalog Number
4 in	12 in	78358559788	LTB412

#### Listings

cULus Classified  
NEMA VE1  
12B Weight Rated

#### Specifications

Material	Aluminum
Grade	6063 T6
12' Span Safe Load	81 lbs/ft
UL Area	0.60 in <sup>2</sup>
AMP Rating	1000
Rung Spacing	9"

#### Characteristics

Stringer Profile	I-Beam
------------------	--------



#### Dimensions- inches (mm)

Height	4.25" (108)
Width	13.5" (343)
Length	144" (3658)

#### Related Products

Standard Splice	LCN4
Support Hanger	LSG4
Hanger Rod Clamp	LHC4
Divider	LD412
Flexible Divider	LDF46

#### Online Resources

Customer Sales Drawings  
eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

