

Aluminum Ladder Tray

Tray Section

NEMA VE1, 12B Load Class

HUBBELL

Features

- Listed to NEMA VE 1 to allow for maximum spans and weight loading.
- For use indoors and also outside in harsh environments.
- Rungs are welded to stringers for strength and continuity.

Ordering Information

Height	Width	UPC Number	Catalog Number
6 in	24 in	78358559793	LTB624

Listings

cULus Classified
NEMA VE1
12B Weight Rated

Specifications

Material	Aluminum
Grade	6063 T6
12' Span Safe Load	89 lbs/ft
UL Area	1.00 in ²
AMP Rating	1200
Rung Spacing	9"

Characteristics

Stringer Profile	I-Beam
------------------	--------



Dimensions- inches (mm)

Height	6.25" (159)
Width	25.5" (648)
Length	144" (3658)

Related Products

Standard Splice	LCN6
Support Hanger	LSG6
Hanger Rod Clamp	LHC6
Divider	LD612
Flexible Divider	LDF66

Online Resources

Customer Sales Drawings
eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

