

Ordering Information

Description	UPC	Catalog Number
For 30A Circuit-Lock® unfused and fused Pin and Sleeve mechanical interlocks	783585258300	MICPK30

Product Type
Plug Kits

Standards

UL Listed
CSA Certified

Specifications

Gaskets	Neoprene
Assembly Screws	Stainless Steel
Hinge Spring	Stainless Steel
Accessory Item	30A Closure Plug

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current.
Dielectric Voltage	Withstands 3,000V AC
Endurance	Mechanical: 10,000 cycles, Electrical: 6,000 cycles
Max. Working Voltage	600V AC RMS
Mechanical	
Impact Resistance	In accordance with UL 746C
Product Identification	Identification and ratings are a part of the external label and molded into the receptacle mount.
Terminal Identification	Terminals identified in accordance with North American and International conventions
Environmental	
Flammability	UL94-5VA and V-0 Classification
Ingress Protection	IP67 Suitability
Operating Temperatures	Max. Continuous: 75° C; Min. Continuous: -40° C w/o impact.

Online Resources

eCatalog
Installation Instructions

