

## Watertight Closure Plug Kits

## Ordering Information

Description	UPC	Catalog Number
For 60 and 100A Circuit-Lock® unfused and fused Pin and Sleeve mechanical interlocks	783585258607	MICPK60

**Product Type**  
Plug Kits

## Standards

UL Listed  
CSA Certified

## Specifications

Gaskets	Neoprene
Assembly Screws	Stainless Steel
Hinge Spring	Stainless Steel
Accessory Item	60A Closure Plug

## Performance

## Electrical

Current Interrupting	Certified for current interrupting at full rated current.
Dielectric Voltage	Withstands 3,000V AC
Endurance	Mechanical: 10,000 cycles, Electrical: 6,000 cycles
Max. Working Voltage	600V AC RMS

## Mechanical

Impact Resistance	In accordance with UL 746C
Product Identification	Identification and ratings are a part of the external label and molded into the receptacle mount.
Terminal Identification	Terminals identified in accordance with North American and International conventions

## Environmental

Flammability	UL94-5VA and V-0 Classification
Ingress Protection	IP67 Suitability
Operating Temperatures	Max. Continuous: 75° C; Min. Continuous: -40° C w/o impact.



## Online Resources

eCatalog  
Installation Instructions