

## Linkosity

**Cordset, Male/Female, Double End, Straight, 4-Wire, 10A  
600V AC, PA Wire Code, 10' Length**

# HUBBELL

### Ordering Information

---

<b>Color</b> Gray	<b>UPC</b> 783585093222	<b>Catalog Number</b> PH1004PA010
----------------------	----------------------------	--------------------------------------

### Specifications

---

Amperage Rating	10 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#12 AWG
Number of Conductors	4-Pole
Special Features	Green/Yellow/Black Wires
Strands	Multi
Voltage Rating	600V kV
Insulation	PVC
Outside Diameter	0.75
Temperature Rating	-20 Deg C to 105 Deg C



### Online Resources

---

[Customer Sales Drawings](#)  
[eCatalog](#)  
[Installation Instructions](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

