

## Linkosity

### Male Female Cable 3A, 2P, 10'

# HUBBELL

## Ordering Information

---

<b>Color</b>	<b>UPC</b>	<b>Catalog Number</b>
Gray	783585505084	PHR302PE010

## Specifications

---

Amperage Rating	30 A
Application	Quick Connect/Disconnect Signal and Control
Conductor Size	#10 AWG
Number of Conductors	2-Pole
Special Features	All Blue Wires
Strands	Multi
Voltage Rating	300V kV
Insulation	PVC
Outside Diameter	0.67
Temperature Rating	-20 Deg C to 105 Deg C



## Online Resources

---

[Customer Sales Drawings](#)  
[eCatalog](#)  
[Installation Instructions](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

