# Switches and Lighting Controls

#### 15A 120/277V AC kV

## **Decorator Series, 2) Single Pole Rockers**

# HUBBELL

#### **Features**

- Smooth, quiet rocker
- Low profile, less than 1 inch deep
- · Self-grounding feature is standard
- · Residential Grade

#### **Ordering Information**

 Color
 UPC
 Catalog Number

 Black
 883778110245
 RCD101BK

#### Listings

CSA Certified UL Listed E3896

### **Specifications**

Action Snap Switch Contact Configuration Two Position

Environmental Conditions Indoor Dry Unless Protected By Additional

Means

Operating Cycles 30,000 Minimum

Operating Temperature Max Continuous- 60 Degrees C, Minimum-

-20 Without Impact

Wattage 4155

# Performance

**Electrical** 

Dielectric voltage Withstands 1,500V AC minimum for 1 minute Endurance 30,000 cycles minimum

Max. working voltage 120V

Overload 1.5 times rating

Mechanical

Terminal accommodation Back and side wire: #14 AWG min. - #12 AWG

max. solid and stranded copper wire only; push

wire: #14 AWG solid copper wire only


Environmental

Flammability UL V-0

Operating Temperatures Maximum continuous 60°C;minimum -20°C

(without impact)





#### **Online Resources**

Customer Sales Drawings eCatalog Installation Instructions

