# Tri-Power Pop Up Counter Receptacles 15A 125V Tamper-Resistant Tri-Power Pop Up Counter Receptacle Surface Mount, Chrome & Color Kit

### Features

- Wireless Charging, A & C USB Ports, and 15 Amp 125 V power outlet all in one
- Spill water tested
- UL Listed for countertop installation
- Permanent installation ready (suitable for MC cable or non-metallic sheath cable)
- Type A and C USB ports
- LED Light indicates power to the ports
- Durable: Push-down to pop-up function is rated for a minimum of 10,000 cycles
- Stability: Firm tower design
- Suitable for 20 Amp circuit, end of line

# **Ordering Information**

DescriptionUPCCatalog Number15A 125V Tamper-Resistant Tri-Power Pop-Up88377831050RCT600CHKitchen Counter Receptacle, Surface MountKitchen Counter Receptacle, Surface MountKitchen Counter Receptacle, Surface Mount

FinishColor/MaterialPolishedChrome

# Listings

UL and cULus listed to UL498, Section 147

# Specifications

Cover and Flange Main Body Wiring Chamber Water Seals Silicone & Die Cast Aluminum Engineered Thermoplastic PBT Die Cast Aluminum Elastomers and Silicon

# Performance

Electrical Receptacle Qi Rating USB A Port USB C Port Circuit Rating Dielectric Voltage

#### Mechanical

Terminal Accommodation Terminal Identification

#### Environmental

Flammability Operating Temperature 15 Amp 125 Volt, Tamper-Resistant Certified 7.5 Watts 5 Amp at 5 Vdc 30 Watts at 9 Vdc 20 Amp non-feed through Withstands 2,000V minimum

#12 AWG copper stranded or solid conductor only Terminals identified in accordance with UL 498 and CSA

UL 94V-2

Maximum continuous 75°C, minimum -40°C (w/o impact)

# Resources

Sales Drawing Catalog Page Installation Instructions





