

Residential Devices

Bi-Pin, Pedestal Type, Low Profile Fluorescent Lamp Holder

HUBBELL

Ordering Information

Color White	UPC 883778112348	Catalog Number RL325
-----------------------	----------------------------	--------------------------------

Listings

UL Listed

Specifications

Voltage Rating	600V AC kV
Application	Medium B-Pin, T8 and T12
Frequency Rating	60 Hz



RL325
SCREW NOT SHOWN
FOR CLARITY
RAPID START LAMP HOLDER



RL325A
RAPID START LAMP HOLDER



RL325B
INSTANT START LAMP HOLDER

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

