

# AV In-Wall Enclosure

## 15A, 125V, 2-Gang

### Recessed TR Duplex Receptacle with Cable Pass Thru

# HUBBELL

#### Features

- Tamper-Resistant (TR) duplex
- Easily mounts to a box
- Cable pass thru organizes and protects low voltage cables

#### Ordering Information

Description	Device Color	UPC	Catalog Number
Smooth face, back and side wired.	Ivory	88377830582	RR1512I

#### Listings

UL Listed to UL 498  
CSA Certified 22.2, No. 42

#### Specifications

Pass Thru Brushes	Nylon
Face	Nylon
Base	PVC
Power Contacts	.030 in. (.8mm) Brass
Ground Contacts	.014 in. (.35mm) Brass
Terminal Screws	Plated Steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc Plated Steel

#### Performance

##### Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum

##### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-12 AWG stranded or solid copper conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

##### Environmental

Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



#### Accessories

Gangable AV Wall Box	HBL985
Recessed TR AV Plastic Box	RR1500

#### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

