Switches, Four Way 15A, 120V AC

Residential Toggle Switch

HUBBELL

Features

- Elongated strap for easier wall box mounting
- Tough thermoplastic with ultrasonically welded cover and base

Ordering Information

DescriptionColorUPC NumberCatalog NumberToggle, Self-Grounding,
Push & Side WireBrown883778101328RS415

Listings

UL Listed E3896 CSA Certified

Specifications

Top Material Plastic
Base Material Plastic
Toggle Material Plastic
Contacts Silver Alloy
Terminal Screws Brass
Auto Grounding Mounting Bridge Zinc-Plated Steel
Ground Screw Steel (Green)

Ground Screw Steel (Green)

Mounting Screw Zinc-Plated Steel

Zinc-Plated Steel

Zinc-Plated Steel

Performance

Electrical

Dielectric Voltage Withstands 1500V AC minimum for 1 minute Max. Continuous Current 15A

Max. Working Voltage 120V AC

Overload Minimum 1.5 times rating
Temperature Rise 30°C maximum at rated current


Environmental

Flammability UL 94 V-2

Operating Temperature Maximum continuous 60°C; minimum -20°C (w/o

impact)





Online Resources

Customer Sales Drawing eCatalog Installation Instructions

