Switches and Lighting Controls 15A 120/277V AC, Illuminated Single Pole

Decorator Switch

Features

- Smooth, quiet rocker
- Self-grounding feature is standard
- Ultrasonically welded cover and base
- Residential Grade

Ordering Information

UPC **Catalog Number** RSD115ILI 883778101175

Listings

CSA Certified Listed to UL Standard 20

Performance

Max. working voltage

Electrical

Withstands 1,500V AC minimum for 1 minute Dielectric voltage Endurance 30,000 cycles minimum

120V

Overload 1.5 times rating

Mechanical

Terminal accommodation Back and side wire: #14 AWG min. - #12 AWG

max. solid and stranded copper wire only; push

wire: #14 AWG solid copper wire only

Environmental


UL V-0 Flammability

Maximum continuous 60°C;minimum -20°C **Operating Temperatures**

(without impact)



HUBBELL



Online Resources

Customer Sales Drawings eCatalog Installation Instructions

