# **Switches and Lighting Controls**

### Three Way, 15A 120/277V AC

## **Decorator Switch**

# HUBBELL

#### **Features**

- Smooth, quiet rocker
- Self-grounding feature is standard
- Ultrasonically welded cover and base
- Residential Grade

#### **Ordering Information**

Color UPC **Catalog Number RSD315I** 883778101243 Ivory

#### Listings

**CSA Certified** UL Listed E3896

#### **Performance**

Max. working voltage

**Electrical** 

Withstands 1,500V AC minimum for 1 minute Dielectric voltage Endurance 30,000 cycles minimum

120V

Overload 1.5 times rating

Mechanical

Terminal accommodation Back and side wire: #14 AWG min. - #12 AWG

max. solid and stranded copper wire only; push

wire: #14 AWG solid copper wire only


**Environmental** 

UL V-0 Flammability

Maximum continuous 60°C;minimum -20°C **Operating Temperatures** 

(without impact)





#### **Online Resources**

**Customer Sales Drawings** eCatalog

