Fire-Rated Poke-Throughs SystemOne Recessed 6-Inch Diameter Core Hole

Features

- One 3/4" EMT for Power, One 2" EMT for Low Voltage
- S1R6CVRBLK, Black Powder Coat Cover Included
- · Sub-Plates Ordered Seperately
- Junction Box Included

Ordering Information

- Fire-Rated Poke-Through Fitting and Cover
- Requires Sub-Plates for Complete Installation

Catalog Number S1R6PTBLK	UPC Number 783585443409	Cover Series S1R6CVR	Core Hole Diameter 6-Inch
Minimum Deck Thickness 2.25" Over Metal Deck	Connection Type Recessed		
Standards			

Specifications

Cover load rating

Access cover material Fire Rating 1000 lbs. static load through 3" diameter mandral Die cast aluminum 1 - 2 Hour Fire Rating

Required

Covers and Sub-Plates

Click here

Accessories

20A USB receptacle with 2 USB charging ports	USB20X2W
20A Self-Test GFCI Receptacle	GFRST20W
20A Decorator Receptacle	DR20WHI
6" Pre-Pour Tube, removed need for core hold drilling	S1R6PPT

Online Resources

Customer Use Drawing eCatalog Installation Instructions





