

Fire-Rated Poke-Throughs

**SystemOne Recessed**

**8-Inch Diameter Core Hole**



**Features**

- One 3/4" EMT for Perimeter Power, One 2" EMT for Center Chamber
- S1R8CVRGRY, Gray Cover Included
- Junction Box Included

**Ordering Information**

- Fire-Rated Poke-Through Fitting, S1R8JNC3 and Cover
- Cover and S1R8JNC3 Installed Onsite

Catalog Number	UPC Number	Cover Series	Core Hole Diameter
S1R8PT3GRY	783585590097	S1R8CVR	8-Inch

Minimum Deck Thickness	Connection Type
2.25" Over Metal Deck	Recessed

**Standards**

cULus & ULC Listed  
UL scrub water compliant  
ADA Compliant

**Specifications**

Cover load rating	1000 lbs. static load through 3" diameter mandral
Access cover material	Die cast aluminum
Fire Rating	1 - 2 Hour Fire Rating

**Required**

Covers and Sub-Plates [Click here](#)

**Accessories**

20A USB receptacle with 2 USB charging ports	USB20X2W
20A Self-Test GFCI Receptacle	GFRST20W
20A Decorator Receptacle	DR20WHI
8" Pre-Pour Tube, removed need for core hold drilling	S1R8PPT

**Online Resources**

Customer Use Drawing  
eCatalog  
Installation Instructions

