

Floor Boxes
Accessories

Rectangular Covers

Features

- Brass Rectangular Duplex Threaded Screw Cover with Brushed Finish
- Includes (2) T40 Torx Slotted Threaded Plugs to Limit Unauthorized Access
- Ships with Mounting Screws and Gasket
- Meets ADA Standards for Accessible Design
- UL514 Scrubwater Compliant

Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Rectangular	Rectangular	783585696324	S3625TR

Listings

cULus Listed
UL 514A Listed and meet UL Scrubwater requirements
CSA C22.2 No 18 certificated

Specifications

Cover Material	Brass
Cover Gasket Material	Elastomer
Cover Spacer	Galvanized Steel

Performance

Mechanical	
Cover Thickness	.12" [3.0mm]
Flange Length	2.99" [76.0mm]
Flange Width	4.16" [105.6mm]

HUBBELL



Related Products

Brass Cover Flange	S5017GR
Brass Surface Flange	SB3083W
Brass Surface Flange	SB3084W
Brass Surface Flange	SB3085W

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

