

Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

Straight and Right Angle Pigtailed Terminal

HUBBELL

- Features
- Transparent housing to inspect contacts
 - Audible SNAP, indicates solid connection
 - Reduces installation time
 - Fully insulated design

Ordering Information

Description	Wire Type	UPC Number	Catalog Number
Right angle, clear terminal with 6-inch leads	Solid	783585541181	SNAP1RAM2

Listings

UL Listed to UL498 File No. E2186
Certified to CSA, C22.2, No. 42 File 285
Fed. Spec. W-C-596

Specifications

Contact	Brass
Terminal Body	PBT
Wire	#12 AWG, T90 Nylon FT-1, PVC 90°C (min)

Performance

Electrical	
Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Terminal Identification	Terminal Wire Leads- Identified in accordance with UL 498
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (w/o impact)



Complementary Products

Mating Receptacle	Hubbell SNAPConnect® Receptacle
-------------------	---------------------------------

Online Resources

Customer Sales Drawing
eCatalog
Installation Instructions

