

SNAPConnect[®] Hospital Grade Receptacle

HUBBELL


- Audible SNAP, indicates solid connection
- Reduces installation time
- Tamper-Resistant, Split Circuit
- Assembled in USA

Description	Device Color	UPC Number	Catalog Number
Hospital Grade, Tamper-Resistant, Split Circuit	Blue	783585542911	SNAP2152BLSCTR A



UL Listed to UL498 File No. E2191
 Certified to CSA, C22.2, No. 42 File 290
 Fed. Spec. W-C-601
 NEMA® WD-6 Compliant

Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass



Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Product Identification Ratings are a permanent part of the device

Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)

Wallplate or Weatherproof Cover
Opening

Customer Sales Drawing
eCatalog
Installation Instructions

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

