

Straight Blade Devices

15 Amp, 125 Volt, 2-Pole, 3-Wire

SNAPConnect[®] Permanently Marked Receptacle



- Features
- Audible SNAP, indicates solid connection
 - Reduces installation time
 - Split Circuit, Fully Controlled
 - Power symbol is clearly visible

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Two Controlled Faces	Black	783585555195	SNAP2152C2BK



- Listings
- UL Listed to UL498 File No. E2203
 - Certified to CSA, C22.2, No. 42 File 302
 - Fed. Spec. W-C-613
 - NEMA[®] WD-6 Compliant

- Complementary Products
- Wallplate or Weatherproof Cover
 - Opening

Specifications

Face	Nylon
Base	Nylon
Line Contact	Brass
Ground Contact	Brass

- Online Resources
- eCatalog

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL 94V-2
Operating Temperature	Maximum continuous 75°C; minimum -40°C (without impact)

